



simturn AX boring-out insert, right-hand CBN, L₂ = 10.2 mm, Ø D_{min}: 4,2mm



Order data

Order number	270579 4,2
GTIN	2050002065918
Item class	24V

Description

Version:

Tool material: CBN8

Technical description

Through-coolant	no
Ø D	4 mm
f	1.95 mm
Radius R	0.15 mm
maximum cutting depth a _{p,max}	0.21 mm
for bores from Ø D _{min}	4.2 mm
Manufacturer's designation	AH9UCBN8
Usable length	10.2 mm
Product name attribute	L ₂ = 10.2 mm
Type of product	Cutter insert for turning

User data

	Suitability	V _c	ISO code
Steel < 67 HRC	suitable		

continuous	suitable
dry	suitable