



simturn AX boring-out insert, right-hand CBN, L₂ = 15.2 mm, Ø D_{min}: 4,2mm



Order data

Order number	270581 4,2
GTIN	2050002065956
Item class	24V

Description

Version:

Tool material: CBN8

Technical description

Radius R	0.15 mm
Ø D	4 mm
f	1.95 mm
for bores from Ø D _{min}	4.2 mm
Through-coolant	no
maximum cutting depth a _{p max}	0.21 mm
Manufacturer's designation	AJ94CBN8
Usable length	15.2 mm
Product name attribute	L ₂ = 15.2 mm
Type of product	Cutter insert for turning

User data

	Suitability	V _c	ISO code
Steel < 67 HRC	suitable		

continuous	suitable
dry	suitable