



**simturn AX boring-out insert, right-hand CBN, L<sub>2</sub> = 35.6 mm, Ø D<sub>min</sub>: 6,2mm**



## Order data

Order number	270589 6,2
GTIN	2050002066076
Item class	24V

## Description

### Version:

Tool material: CBN8

## Technical description

Through-coolant	no
for bores from Ø D <sub>min</sub>	6.2 mm
Radius R	0.2 mm
maximum cutting depth a <sub>p max</sub>	0.31 mm
Ø D	6 mm
f	2.95 mm
Manufacturer's designation	ANYTCBN8
Usable length	35.6 mm
Product name attribute	L <sub>2</sub> = 35.6 mm
Type of product	Cutter insert for turning

## User data

	Suitability	V <sub>c</sub>	ISO code
Steel < 67 HRC	suitable		

continuous	suitable
dry	suitable