



simturn AX boring-out insert, right-hand CBN, L₂ = 20.3 mm, Ø D_{min}: 6,2mm



Order data

Order number	270583 6,2
GTIN	2050002066014
Item class	24V

Description

Version:

Tool material: CBN8

Technical description

maximum cutting depth $a_{p\max}$	0.31 mm
f	2.95 mm
for bores from Ø D _{min}	6.2 mm
Radius R	0.2 mm
Through-coolant	no
Ø D	6 mm
Manufacturer's designation	AEWGCBN8
Usable length	20.3 mm
Product name attribute	L ₂ = 20.3 mm
Type of product	Cutter insert for turning

User data

	Suitability	V _c	ISO code
Steel < 67 HRC	suitable		

continuous	suitable
dry	suitable