


**simturn AX boring-out insert, right-hand CBN, L<sub>2</sub> = 10.2 mm, Ø D<sub>min</sub>: 3,2mm**


## Order data

Order number	270579 3,2
GTIN	2050002065901
Item class	24V

## Description

### Version:

Tool material: CBN8

## Technical description

Ø D	4 mm
maximum cutting depth a <sub>p max</sub>	0.16 mm
Through-coolant	no
Radius R	0.15 mm
f	1.45 mm
for bores from Ø D <sub>min</sub>	3.3 mm
Manufacturer's designation	ADD4CBN8
Usable length	10.2 mm
Product name attribute	L <sub>2</sub> = 10.2 mm
Type of product	Cutter insert for turning

## User data

	Suitability	V <sub>c</sub>	ISO code
Steel < 67 HRC	suitable		

continuous	suitable
dry	suitable