



**simturn AX boring-out insert, right-hand CBN, L<sub>2</sub> = 30.5 mm, Ø D<sub>min</sub>: 5,2mm**



## Order data

Order number	270587 5,2
GTIN	2050002066052
Item class	24V

## Description

### Version:

Tool material: CBN8

## Technical description

maximum cutting depth $a_{p\max}$	0.26 mm
for bores from Ø D <sub>min</sub>	5.2 mm
Through-coolant	no
Radius R	0.2 mm
Ø D	5 mm
f	2.45 mm
Manufacturer's designation	ADNSCBN8
Usable length	30.5 mm
Product name attribute	L <sub>2</sub> = 30.5 mm
Type of product	Cutter insert for turning

## User data

	Suitability	V <sub>c</sub>	ISO code
Steel < 67 HRC	suitable		

continuous	suitable
dry	suitable