


simturn AX Center Line boring-out insert, right-hand CBN, L2 = 6.1 mm, Ø Dmin: 1 mm


Order data

Order number	270521 1
GTIN	2050002064874
Item class	24V

Description

Version:

Tool material = CBN8

Technical description

Radius R	0.1 mm
f	1.95 mm
Through-coolant	no
maximum cutting depth $a_{p\max}$	0.05 mm
Ø D	4 mm
Manufacturer's designation	ADCNCBN8
Usable length	6.1 mm
Product name attribute	L ₂ = 6.1 mm
Type of product	Cutter insert for turning

User data

	Suitability	V _c	ISO code
Steel < 67 HRC	suitable		
continuous	suitable		

wet minimum	suitable
dry	suitable
Air	suitable