



## simturn AX Center Line, boring-out insert, right-hand, L<sub>2</sub> = 6.1 mm, Ø D<sub>min</sub>: 1mm



### Order data

Order number	270503 1
GTIN	2050002064645
Item class	24U

### Description

#### Version:

Coating: X800 (successor to coating GN39)

### Technical description

max. groove depth t <sub>max</sub>	0.1 mm
for bores from Ø D <sub>min</sub>	1 mm
f	1.95 mm
Through-coolant	no
Radius R	0.1 mm
Ø D	4 mm
Manufacturer's designation	AJGFX800
Usable length	6.1 mm
Product name attribute	L <sub>2</sub> = 6.1 mm
Type of product	Cutter insert for turning

### User data

	Suitability	V <sub>c</sub>	ISO code
--	-------------	----------------	----------

Aluminium (short chipping)	suitable only under restricted conditions		
Alu > 10% Si	suitable only under restricted conditions		
Steel < 500 N/mm <sup>2</sup>	suitable	180 m/min	P
Steel < 900 N/mm <sup>2</sup>	suitable	130 m/min	P
INOX < 900 N/mm <sup>2</sup>	suitable	100 m/min	M
INOX > 900 N/mm <sup>2</sup>	suitable	70 m/min	M
Ti > 850 N/mm <sup>2</sup>	suitable only under restricted conditions		S
GG(G)	suitable	110 m/min	K
CuZn	suitable		
continuous	suitable		
irregular	suitable only under restricted conditions		
wet maximum	suitable		