



## simturn AX Center Line boring-out insert, right-hand CBN, L2 = 6.1 mm, Ø Dmin: 1,4mm



### Order data

Order number	270521 1,4
GTIN	2050002064881
Item class	24V

### Description

#### Version:

Tool material = CBN8

### Technical description

Through-coolant	no
maximum cutting depth $a_{p\max}$	0.07 mm
Ø D	4 mm
Radius R	0.1 mm
f	1.95 mm
Manufacturer's designation	AW34CBN8
Usable length	6.1 mm
Product name attribute	L <sub>2</sub> = 6.1 mm
Type of product	Cutter insert for turning

### User data

	Suitability	V <sub>c</sub>	ISO code
Steel < 67 HRC	suitable		
continuous	suitable		

wet minimum	suitable
dry	suitable
Air	suitable