



simturn AX Center Line boring-out insert, right-hand CBN, L₂ = 10.2 mm, Ø D_{min}: 1,4mm



Order data

| | |
|--------------|---------------|
| Order number | 270523 1,4 |
| GTIN | 2050002064898 |
| Item class | 24V |

Description

Version:

Tool material = CBN8

Technical description

| | |
|--|---------------------------|
| Radius R | 0.1 mm |
| maximum cutting depth a _{p,max} | 0.07 mm |
| f | 1.95 mm |
| Ø D | 4 mm |
| Through-coolant | no |
| Manufacturer's designation | AW36CBN8 |
| Usable length | 10.2 mm |
| Product name attribute | L ₂ = 10.2 mm |
| Type of product | Cutter insert for turning |

User data

| | Suitability | V _c | ISO code |
|----------------|-------------|----------------|----------|
| Steel < 67 HRC | suitable | | |
| continuous | suitable | | |

| | |
|-------------|----------|
| wet minimum | suitable |
| dry | suitable |
| Air | suitable |