


simturn AX Center Line boring-out insert, right-hand CBN, L₂ = 10.2 mm, Ø D_{min}: 2,7mm


Order data

Order number	270523 2,7
GTIN	2050002064904
Item class	24V

Description

Version:

Tool material = CBN8

Technical description

Radius R	0.15 mm
maximum cutting depth $a_{p\max}$	0.13 mm
Through-coolant	no
f	1.95 mm
Ø D	4 mm
Manufacturer's designation	APSVCBN8
Usable length	10.2 mm
Product name attribute	L ₂ = 10.2 mm
Type of product	Cutter insert for turning

User data

	Suitability	V _c	ISO code
Steel < 67 HRC	suitable		
continuous	suitable		

wet minimum	suitable
dry	suitable
Air	suitable