



simturn AX Center Line boring-out insert, right-hand CBN, L₂ = 10.2 mm, Ø D_{min}: 3,2mm



Order data

Order number	270523 3,2
GTIN	2050002064911
Item class	24V

Description

Version:

Tool material = CBN8

Technical description

f	1.95 mm
Ø D	4 mm
Through-coolant	no
Radius R	0.15 mm
maximum cutting depth a _{p max}	0.16 mm
Manufacturer's designation	APBYCBN8
Usable length	10.2 mm
Product name attribute	L ₂ = 10.2 mm
Type of product	Cutter insert for turning

User data

	Suitability	V _c	ISO code
Steel < 67 HRC	suitable		
continuous	suitable		

wet minimum	suitable
dry	suitable
Air	suitable