


simturn AX Center Line boring-out insert, right-hand CBN, L₂ = 15.2 mm, Ø Dmin: 3,7mm


Order data

Order number	270525 3,7
GTIN	2050002064959
Item class	24V

Description

Version:

Tool material = CBN8

Technical description

Through-coolant	no
Ø D	4 mm
f	1.95 mm
Radius R	0.15 mm
maximum cutting depth $a_{p\max}$	0.18 mm
Manufacturer's designation	AJ9YCBN8
Usable length	15.2 mm
Product name attribute	L ₂ = 15.2 mm
Type of product	Cutter insert for turning

User data

	Suitability	V _c	ISO code
Steel < 67 HRC	suitable		
continuous	suitable		

wet minimum	suitable
dry	suitable
Air	suitable