

Garant UNILINE

**UNI Z-Tower stationary U-shape, Type: L****Order data**

Order number	955454 L
GTIN	4062406785536
Item class	9GC

**Description****Version:**

Semi-high UNI Z-Tower with 25 mm thick bamboo worktop. All sides inside and outside with perforated panels  $\square$  9x9 mm on a 37 mm grid for attaching perforated panel accessories and Easyfix hooks and holders. Brush strip at the rear for routing cables and additional cable pass-through. Presentable modular provision system for direct access to work materials and quick visualisation of information. Versatile and general-purpose use for various different applications and fittings. Fitting of drawers only possible in size M.

**Colour:**

Two-tone **powder-coated**, silver combined with anthracite RAL 7016. **Not configurable.**

**Note:**

Accessories such as marking boards, attachments, pictograms, storage shelves, drawers, doors and push handles can be found under No. 955474 – 955499.

**Technical description**

Depth	750 mm
Height	1920 mm
Usable width	690 mm

Weight	86 kg
Series	Z-Tower
Width	750 mm
Usable depth	510 mm
Usable height of tower compartment	850 mm
Worktop thickness	25 mm
Hoffmann perforated panel grid interval	9×9
Height adjustment interval	37
Type of product	Perforated panel tower