

Garant UNILINE

UNI Z-Tower stationary U-shape, Type: SM**Order data**

Order number	955454 SM
GTIN	4062406785512
Item class	9GC

Description**Version:**

Semi-high UNI Z-Tower with 25 mm thick bamboo worktop. All sides inside and outside with perforated panels \square 9x9 mm on a 37 mm grid for attaching perforated panel accessories and Easyfix hooks and holders. Brush strip at the rear for routing cables and additional cable pass-through. Presentable modular provision system for direct access to work materials and quick visualisation of information. Versatile and general-purpose use for various different applications and fittings. Fitting of drawers only possible in size M.

Colour:

Two-tone **powder-coated**, silver combined with anthracite RAL 7016. **Not configurable.**

Note:

Accessories such as marking boards, attachments, pictograms, storage shelves, drawers, doors and push handles can be found under No. 955474 – 955499.

Technical description

Width	750 mm
Usable depth	510 mm
Series	Z-Tower

Usable width	540 mm
Weight	69 kg
Depth	750 mm
Height	945 mm
Usable height of tower compartment	850 mm
Worktop thickness	25 mm
Hoffmann perforated panel grid interval	9×9
Height adjustment interval	37
Type of product	Perforated panel tower