

Garant GRIDLINE

ToolTruck mobile workbench for L-BOXX®, Type: 4



Order data

Order number	914574 4
GTIN	4062406785581
Item class	9GT

Description

Version:

The ToolTruck mobile workbench has a worktop of X-ABS for highly demanding technical applications. Open compartment with 4 pull-out shelves, suitable for 4 pcs. L-BOXX® modular plastic cases, which can be quickly and easily engaged and released. 2 pcs. each L-BOXX® modular plastic case No. 693330 size 102 and size 136 will fit. Or alternatively: 2 pcs. No. 693330 size 102; 1 pc. size 238 (if 3rd pull-out shelf removed). **Cabinet stiles are clad with LDPE bumpers. Central locking** locks door, drawers and pull-out shelves. Cupboard section with door and 2 storage shelves.

Colour:

Two-tone **powder-coated**, silver combined with RAL 7016 anthracite.

Note:

Optional storage shelf / side compartment No. 914791 not integrated into the ToolTruck central locking system, locked instead by a separate cylinder lock. See group 95 for further accessories and dividing material. Carrying case L-BOXX® is not included.

Technical description

Number of castors with parking brake	2
Depth	500 mm
Series	ToolTruck

Bumper	yes
can be lowered	no
Weight	89 kg
Number of fixed wheels without parking brake	2
Width	1195 mm
Number of doors	1
Individual drawer release system	One-hand
Height	1000 mm
Material of worktop	X-ABS
Pull-out shelf usable width	370 mm
Drawer/pull-out shelf load capacity	40 kg
Drawer runner extension (partial/full extension)	100 %
Drawer runner extension	Anti-tilt lock
Hoffmann perforated panel grid interval	9×9 mm
Cylinder lock	modular barrel
Type of product	mobile workbench

Accessories

Set of wheels for roller cabinets and mobile workbenches Type G	915567 G
Lock plate for GridLine Type VA21	914227 VA21