



Cordless impact wrench / impact driver, Type: GDS18V1000



Order data

Order number	074052 GDS18V1000
GTIN	4059952564586
Item class	03B

Description

Version:

Cordless impact wrench / impact driver.

- **Reversible.**
- **Battery charge display.**

Powerful 18V impact wrench with **BITURBO** brushless technology, for the **most demanding** screw tightening in metal.

- **3 speed/torque settings for excellent control of speed and torque.**

Supplied with:

Supplied with 2× Li-ion batteries, charger, L-BOXX

Note:

Suitable replacement batteries and chargers can be found under No. 073851 – 073867.

Technical description

Tool arbor drive profile	External square drive
maximum screw Ø (8.8 - 12.9)	M24
Packaging	Modular case (L-Boxx)
suitable battery - supplier / battery type / voltage	Bosch 18 V
Battery voltage	18 V

Weight	2.9 kg
Tool arbor size	1/2 in
Number of impacts	0 - 2600 min ⁻¹
Number of rechargeable batteries contained	2
maximum torque hard	1000 Nm
typical application	Heavy Duty
Manufacturer's designation	GDS18V-1000
Power supply	Rechargeable battery-powered
Battery capacity	8 Ah
Type of rechargeable battery	Lithium-ion
maximum vibration to EN	13.5 m/s ²
maximum break-away torque	1600 Nm
Torque settings	3
Type of product	Impact wrench