


**Fibre disc Actirox AF 799 (CER), Ø 115 mm, Grit: 36****Order data**

Order number	566447 36
GTIN	4018875878620
Item class	56V

Description**Version:**

Tear-resistant but very flexible **vulcanised fibre**. Bore diameter 22.23 mm and crossed slots. Top type VSM Actrirox AF 799 fibre discs **with very high and aggressive grinding performance**. Cool grinding and outstanding tool life.

Grit type: **100% geometrically shaped VSM ceramic grit**.

Application:

Limited to maximum 80 m/s circumferential speed with backing pads No. 566650 / 6670 on angle grinders. For **grinding flat and curved surfaces** with a high degree of **flexibility**.

Technical description

Disc Ø	115 mm
Grit	36
Series	Actirox
Grinding media	Ceramic grit
Grinding medium code	Ceramic

Grinding media backing	Vulcanised fibre
Iron, sulphur and chlorine constituents	< 0.1 %
Product name attribute	Ø 115 mm
Bore Ø	22.23 mm
optimised for material	Non-ferrous metals
optimised for material	Cast iron
optimised for material	wood
maximum circumferential speed	80 m/s
Type of product	Fibre disc

User data

	Suitability	V _c	ISO code
Alu Mg	suitable only under restricted conditions		
Steel < 900 N/mm ²	suitable		
Steel < 1400 N/mm ²	suitable		
Steel < 55 HRC	suitable		
Steel < 60 HRC	suitable		
Steel < 67 HRC	suitable		
INOX	suitable only under restricted conditions		
Ti	suitable only under restricted conditions		
GG(G)	suitable		
CuZn	suitable		
dry	suitable		