

**Cordless drill / driver without battery, Type: GSR18V150C****Order data**

Order number	070246 GSR18V150C
GTIN	4059952523217
Item class	03B

Description**Version:**

- **Compact, powerful cordless drill with forward/reverse operation.**
- **LED light to illuminate the working area and battery charge display.**
- **Multi-stage torque setting for precise screw driving.**
- **Electronic speed control for precise drilling and screw driving.**
- **Softgrip.**

Can be retrofitted with a **connectivity** module.

Supplied with:

Including L-BOXX and additional handle, **without** battery and charger.

Note:

See from No. 073851 and No. 073863 – 073867 for suitable replacement batteries, starter sets and chargers.

Technical description

Motor design	Brushless motor
suitable battery - supplier / battery type / voltage	Bosch 18 V
Quick-clamping chuck range	1.5 - 13 mm

Weight	2.1 kg
Interface	Bluetooth interface
maximum twist drill size Ø in wood	150 mm
Speed range 2nd speed	0 - 2200 min ⁻¹
Manufacturer's designation	GSR18V-150C
Number of rechargeable batteries contained	0
maximum torque soft	84 Nm
Battery voltage	18 V
maximum vibration to EN	2.5 m/s ²
Type of rechargeable battery	Lithium-ion
maximum torque hard	150 Nm
Packaging	Modular case (L-Boxx)
Power supply	Rechargeable battery-powered
typical application	Heavy Duty
Speed range 1st speed	0 - 550 min ⁻¹
maximum twist drill size Ø in steel	16 mm
Type of product	Drill/driver
USP1	18V
USP2	Brushless motor, with softgrip, without battery, in L-Boxx