



## Cordless heat gun, Type: GHG18V50



### Order data

Order number	078334 GHG18V50
GTIN	4059952586694
Item class	03B

### Description

#### Version:

Cordless heat gun with 2 temperature settings (300° / 500°)

- **Quick heating, only 6 seconds to 300°.**
- **LED light to illuminate the working area.**
- **Compatible with all nozzles for cable-connected heat guns from Bosch.**

#### Supplied with:

**Without battery, without charger.** Incl. L-BOXX, reflector nozzle and reducer nozzle.

#### Note:

Suitable batteries, starter sets and chargers for the Bosch 18V system can be found under No. 073851 – No. 073858 and No. 073863 – No. 073867.

### Technical description

Power supply	Mains operated
Manufacturer's designation	GHG18V-50
Number of rechargeable batteries contained	0
Weight	590 g

Air temperature	300 - 500 °C
Air flow volume	175 l/min
Type of rechargeable battery	Lithium-ion
Packaging	Modular case (L-Boxx)
Battery voltage	18 V
Number of temperature levels	2
suitable battery - supplier / battery type / voltage	Bosch 18 V
Type of product	Hot air pistol