

**Cordless impact wrench / impact driver, Type: GDS1050HC****Order data**

Order number	074052 GDS1050HC
GTIN	4059952548616
Item class	03B

Description**Version:**

Cordless impact wrench / impact driver.

- **Reversible.**
 - **Battery charge display.**
- 3/4 inch impact wrench with **BITURBO** brushless technology and **Bluetooth connectivity**.
- **3 speed/torque settings.**
 - **2 operating modes for metal and wood.**
 - **Further parameters can be set individually using the Toolbox app.**

Supplied with:

Supplied with 2x Li-ion batteries, charger, L-BOXX

Note:

Suitable replacement batteries and chargers can be found under No. 073851 – 073867.

Technical description

maximum torque hard	1050 Nm
maximum screw Ø (8.8 - 12.9)	M24
typical application	Heavy Duty
Tool arbor size	3/4 in

Packaging	Modular case (L-Boxx)
Battery voltage	18 V
maximum vibration to EN	13.5 m/s ²
Type of rechargeable battery	Lithium-ion
Number of rechargeable batteries contained	2
Number of impacts	0 - 2600 min ⁻¹
suitable battery - supplier / battery type / voltage	Bosch 18 V
Tool arbor drive profile	External square drive
Power supply	Rechargeable battery-powered
Weight	2.9 kg
Battery capacity	8 Ah
Manufacturer's designation	GDS18V-1050HC
maximum break-away torque	1700 Nm
Torque settings	3
Interface	Bluetooth interface
Type of product	Impact wrench