



## Eco cut knurling tool universal, Shank size: 20mm



### Order data

Order number	290242 20
GTIN	4030741949432
Item class	29H

### Description

#### Version:

Grub screws in the shank for clearance angle correction.

**Modular design: Can be used universally as right-hand or left-hand version.** Adjustment of the production  $\varnothing$  using a scale.

### Technical description

for knurl width w	6 mm
Carbide sleeve, cover disc, screw	299920 9
for knurl $\varnothing d_1$	25 mm
Working range	10 - 250 mm
for knurl bore $\varnothing d_2$	8 mm
Cutting direction	left-hand and right-hand
for knurl profile	RGE30° 2×AA
for knurl profile	RGE45° BL/BR15°
Type of product	Self-centering knurling tool

