



Stereo microscope with incident illumination, without lighting, Type: M50



Order data

| | |
|--------------|---------------|
| Order number | 491753 M50 |
| GTIN | 7630003572254 |
| Item class | 49B |

Description

Version:

- **Modular product range and thus optimum adaptation of the microscope to the application.**
- **Parfocal matching optics system: When the magnification is changed, sharpness remains constant.**
- **Ergonomic design.**
- **ESD version avoids damage due to static discharges.**

Five-stage magnification changer: 6.3x; 10x; 16x; 25x; 40x.

Supplied with:

Lens carrier, binocular inclined tube 45°, 2x eyepieces suitable for glasses wearers, lens achromat 1.0x, stand, dust cover (antistatic).

Incident illumination incl. table insert black/white.

Optional extras:

LED illumination No. 491755 and transillumination No. 491777 size BLI.

Note:

Note the scope of supply, since product images may vary slightly.

Technical description

| | |
|-------------------------|--------------------|
| Zoom | 5:1 |
| Optics system | Greenough parfocal |
| Depth of focus | 13.7 mm |
| Field of vision Ø | 5.75 - 36.5 mm |
| Magnification (x-times) | 6.3 - 40 |
| Base width | 278 mm |
| Eyepiece | 10×/23B |
| Working distance | 89.6 mm |
| Series | M |
| Base length | 301 mm |
| Type of product | Stereo microscope |