



## Stereo microscope with swingarm stand, without lighting, Type: M50



### Order data

Order number	491754 M50
GTIN	2050002078222
Item class	49B

### Description

#### Version:

- **Modular product range and thus optimum adaptation of the microscope to the application.**
- **Parfocal matching optics system: When the magnification is changed, sharpness remains constant.**
- **Ergonomic design.**
- **ESD version avoids damage due to static discharges.**

Five-stage magnification changer: 6.3×; 10×; 16×; 25×; 40×.

#### Supplied with:

Lens carrier, binocular inclined tube 45°, 2× eyepieces suitable for glasses wearers, lens achromat 1.0×, stand, dust cover (antistatic).

Swingarm stand.

#### Optional extras:

LED illumination No. 491755 and transillumination No. 491777 size BLI.

#### Note:

Note the scope of supply, since product images may vary slightly.

### Technical description

Base length	260 mm
Depth of focus	13.7 mm
Working distance	89.6 mm
Optics system	Greenough parfocal
Magnification (x-times)	6.3 - 40
Series	M
Eyepiece	10×/23B
Field of vision Ø	5.75 - 36.5 mm
Zoom	5:1
Base width	220 mm
Type of product	Stereo microscope