



## Stereo microscope with swingarm stand, without lighting, Type: M80



### Order data

Order number	491754 M80
GTIN	2050002078246
Item class	49B

### Description

#### Version:

- **Modular product range and thus optimum adaptation of the microscope to the application.**
- **Parfocal matching optics system: When the magnification is changed, sharpness remains constant.**
- **Ergonomic design.**
- **ESD version avoids damage due to static discharges.**

Zoom positions: 8 configurable positions, for repetitive tasks. Base plate with anti-shock.

#### Supplied with:

Lens carrier, binocular inclined tube 45°, 2× eyepieces suitable for glasses wearers, lens achromat 1.0×, stand, dust cover (antistatic).

Swingarm stand.

#### Optional extras:

LED illumination No. 491755 and transillumination No. 491777 size BLI.

#### Note:

Note the scope of supply, since product images may vary slightly.

### Technical description

Base width	220 mm
Optics system	Greenough parfocal
Eyepiece	10×/23B
Base length	330 mm
Depth of focus	13.7 mm
Field of vision Ø	3.8 - 30.7 mm
Magnification (x-times)	7.5 - 60
Working distance	83.4 mm
Series	M
Zoom	8:1
Type of product	Stereo microscope