

Garant**Solid carbide extension for screw-in milling cutters $\varnothing d = 12$ mm, Thread M \times L: M6X90****Order data**

Order number	301361 M6X90
GTIN	4062406785666
Item class	31Z

Description**Version:**

Solid carbide extension with vibration-damping properties, shank tolerance h6, long and slim version.

Application:

Particularly for use in shrink-fit chucks. Perfect combination of standard steel extensions and Densimet® extensions.

Technical description

Bore $\varnothing D_1$	6.5 mm
Shank $\varnothing d$	12 mm
Overall length L_{tot}	90 mm
External $\varnothing D$	9.8 mm
Thread M	M6
Reach L_1	40 mm
Adapter	$\varnothing d = 12$ mm
Through-coolant	yes
Vibration	damped
Type of product	Extension

