

**Garant**

**Solid carbide extension for screw-in milling cutters Ø d = 20 mm, Thread M × L: M10X100**

**Order data**

Order number	301384 M10X100
GTIN	4062406786120
Item class	31Z

**Description****Version:**

Solid carbide extension with vibration-damping properties, shank tolerance h6, long and slim version.

**Application:**

Particularly for use in shrink-fit chucks. Perfect combination of standard steel extensions and Densimet® extensions.

**Technical description**

Bore Ø D <sub>1</sub>	10.5 mm
Shank Ø d	20 mm
Thread M	M10
Overall length L <sub>tot</sub>	100 mm
Reach L <sub>1</sub>	40 mm
External Ø D	15.4 mm
Through-coolant	yes
Vibration	damped
Type of product	Extension

