



## ER clamping nut CENTRO P HDC, Type HDC for ER: 32HDC



### Order data

Order number	309657 32HDC
GTIN	2050002068797
Item class	34F

### Description

#### Version:

With trapezoidal fine thread for high clamping forces. Extra long double guidance of the ER clamping nut. Ball-bearing clamping nut for higher tightening torques.

#### Suitable for:

**FAHRION ER collet chucks HDC.**

#### Optional extras:

Precision ER collets No. 308981 – 308986, HP No. 309376 – 309378 and for tapping collets No. 309414 / 309418, roller bearing wrenches HDC No. 309754 / 309756.

#### Note:

**FAHRION ER clamping nuts type HDC not suitable for ER CENTRO P collet chucks.**

Clamping range: 2 - 20 mm

Overall length L: 27 mm

External Ø D: 53 mm

maximum tightening torque: 180 N·m

Thread: Tr42×1

### Technical description

Clamping range	2 - 20 mm
----------------	-----------

External Ø D	53 mm
maximum tightening torque	180 N·m
Overall length L	27 mm
Thread	Tr42×1
Type of product	Clamping nut