



simturn AX Center Line boring-out insert, right-hand CBN, L₂ = 20.3 mm, Ø D_{min}: 3,7mm



Order data

Order number	270527 3,7
GTIN	2050002064973
Item class	24V

Description

Version:

Tool material = CBN8

Technical description

Ø D	4 mm
Radius R	0.15 mm
maximum cutting depth a _{p max}	0.18 mm
f	1.95 mm
Through-coolant	no
Manufacturer's designation	AHN6CBN8
Usable length	20.3 mm
Product name attribute	L ₂ = 20.3 mm
Type of product	Cutter insert for turning

User data

	Suitability	V _c	ISO code
Steel < 67 HRC	suitable		
continuous	suitable		

wet minimum	suitable
dry	suitable
Air	suitable