

Garant
Boring bar for grooving, left-hand, Type: 20/2

Order data

| | |
|--------------|---------------|
| Order number | 274171 20/2 |
| GTIN | 4062406790318 |
| Item class | 21U |

Description
Version:

For cutter inserts No. 275000 – 275015.

Application:

For grooving from diameter $D_{\min} = 14$ mm.

Attention:

Please order the assembly key No. 279940 separately.

Technical description

| | |
|--|--------------------------|
| Minimum pre-drill $\varnothing D_{\min}$ | 16 mm |
| Overhang L_1 recessed holders | 30 mm |
| t_{\max} internal machining | 3 mm |
| Groove width w | 1.5 mm |
| Shank $\varnothing D_s$ | 20 mm |
| Overall length L | 88 mm |
| Application range | radial internal grooving |
| Application type | left-hand |
| Through-coolant | yes |
| System key | yes |
| axial grooving possible | no |

Type of product

Boring bar