

Garant**Boring bar for grooving, right-hand, Type: 16/2****Order data**

| | |
|--------------|---------------|
| Order number | 274170 16/2 |
| GTIN | 4062406785468 |
| Item class | 21U |

Description**Version:**

For cutter inserts No. 275000 – 275015.

Application:

For grooving from diameter $D_{\min} = 14$ mm.

Attention:

Please order the assembly key No. 279940 separately.

Technical description

| | |
|--|------------|
| Overhang L_1 recessed holders | 25 mm |
| t_{\max} internal machining | 3 mm |
| Shank $\varnothing D_s$ | 16 mm |
| Groove width w | 1.5 mm |
| Overall length L | 78 mm |
| Minimum pre-drill $\varnothing D_{\min}$ | 14 mm |
| Application type | right-hand |
| Through-coolant | yes |
| System key | yes |
| axial grooving possible | no |
| Type of product | Boring bar |

