



Hydraulic sets, Type: ECO



Order data

Order number	086052 ECO
GTIN	7391390487889
Item class	08Y

Description

Version:

Ready-for-use hydraulic sets in a working range of 700 bar with all the necessary components for connection to common single-acting and double-acting hydraulic cylinders.

- **2-stage 1.0 litre hand pump for rapid work progression.**
- **100% pressure-tested hoses for a maximum pressure of 720 bar, manufactured to ISO 22384.**
- **As standard with the CEJN CIS hose identification system for maximum safety.**
- **3/8 inch NPT connection thread, coupling system to ISO 14540. Compatibility with more than 80% of the hydraulic systems available on the market.**
- **All components can be reordered individually.**

Entry-level set with all the necessary basic components.

Supplied with:

Hydraulic pump, hose set, connection adaptor, **without oil filling.**

Note:

Hydraulic pumps must be filled with hydraulic oil before use. We recommend using oils to ISO VG 15 or ISO VG 22.

Technical description

Hydraulic connection	3/8 NPT in
Working pressure	700 bar

Number of pressure stages	2
usable tank volume	1000 ml
Hose length	2 m
Type of product	Hydraulic set