



## Hydraulic sets, Type: PRO



### Order data

Order number	086053 PRO
GTIN	7391390484079
Item class	08Y

### Description

#### Version:

Ready-for-use hydraulic sets in a working range of 700 bar with all the necessary components for connection to common single-acting and double-acting hydraulic cylinders.

- **2-stage 1.0 litre hand pump for rapid work progression.**
- **100% pressure-tested hoses for a maximum pressure of 720 bar, manufactured to ISO 22384.**
- **As standard with the CEJN CIS hose identification system for maximum safety.**
- **3/8 inch NPT connection thread, coupling system to ISO 14540. Compatibility with more than 80% of the hydraulic systems available on the market.**
- **All components can be reordered individually.**

Professional set with additional components for efficient and rapid work progress.

- **Hose set with coupling and coupling adaptor for quick attachment and separation of the components.**
- **Pressure gauge for monitoring pressure.**
- **Sturdy ABS case with foam inlay for secure storage and easy transport to the place of use.**

#### Supplied with:

Hydraulic pump, hose set with coupling adaptor and coupling, pressure gauge, connection block, coupling for the cylinder side, sturdy transport case, **without oil filling.**

#### Note:

Hydraulic pumps must be filled with hydraulic oil before use. We recommend using oils to ISO VG 15 or ISO VG 22.

---

## Technical description

Number of pressure stages	2
usable tank volume	1000 ml
Working pressure	700 bar
Hydraulic connection	3/8 NPT in
Hose length	2 m
Packaging	Carrying case
Type of product	Hydraulic set