

ELTEN**Shoe, black/red HANNAH XXTL low ESD, S3, EU shoe size: 36**

Order data

Order number	092747 36
GTIN	4030839354131
Item class	09P

Description

Version:

Ladies' safety shoes HANNAH XXTL Low.

- **Hydrophobic upper material made of microfibre and textile.**
- **Breathable textile lining.**
- **Padded tongue.**
- **ESD PRO Lady X full-size insole.**
- **WELLMAXX TRAINERS LADY PU/PU outer sole, anti-slip.**
- **Sole core of Infinergy® from BASF for shock absorption over the entire sole.**
- **Leather-free.**
- **ESD security.**

Standard:

EN ISO 20435:2011 S3 SRC.

Characteristic of the sole: Rebound sole

Protection class: S3

Material of protective toe-cap: Steel

Puncture resistance: Tekstil

Standard: Inlay type-tested according to DGUV regulation 191

Technical description

Protection class	S3
------------------	----

Standard	Inlay type-tested according to DGUV regulation 191
Material of protective toe-cap	Steel
Puncture resistance	Tekstil
EU shoe size	36
Gender	Ladies
electrostatic characteristic	EGB/ESD
Characteristic of the sole	Rebound sole
Type of product	Safety shoes