



Powered air respirator with integral head and face protection PowerCap® Infinity®, Type: SET



Order data

Order number	097150 SET
GTIN	5038428302722
Item class	09W

Description

Version:

The **PowerCap® Infinity®** combines **3 types of protection** in a single product. The powered air respirator system provides respiratory protection against particles, the EVO®5 industrial safety helmet provides head protection, and the visor protects the eyes and face. **The protection can be extended by attaching JSP ear defenders.**

Powered air respirator: With a blower performance of 160 l/min without resistance to breathing and without the visor misting up, the PowerCap® Infinity® guarantees protection against particles to EN 12941 TH3P. Incl. quick-change bayonet system.

Head protection: The PowerCap® Infinity® is based on the EVO®5 industrial safety helmet, which satisfies EN 397. Thanks to the ABS shell, the helmet offers all-day protection and is very comfortable due to the Evolution® 3D-Adjustment™ strap system.

Eye and face protection: The PowerCap® Infinity offers eye protection to EN 166. The visor protects the entire face against flying particles.

Standard:

EN 397, EN 12941 Schutzstufe TH3P, EN 166.

Supplied with:

1× PowerCap® Infinity®, 1× rechargeable battery, 1× charging station, 1× pair of TH3 particle filters, 1× pair of pre-filters, 1× airflow indicator, 1× bag.

Note:

Please observe the document in the packaging for the training videos on the PowerCap® Infinity®!

Technical description

Manufacturer's designation	CEA646-001-100
Type of product	Respirator blower unit

Accessories

Spare battery Type CHARGE	097155 CHARGE
Charging station and mains adapter Type BATTERY	097154 BATTERY
Replacement filter set Type P3	097151 P3
Spare visor Type VISOR	097152 VISOR
Peel off visor set, 10 pieces Type FOIL	097153 FOIL
Helmet strap Type STRAP	097156 STRAP
Replacement filter set Type VF	097151 VF