



Precision dial indicator, shock-resistant, Measuring range / Body Ø: 1/61,5mm



Order data

Order number	433407 1/61,5
GTIN	7630041151848
Item class	45A

Description

Version:

Strong, satin chrome plated brass casing; unbreakable dial glass. Clamping shank \varnothing 8 mm h6, hardened and ground. High accuracy version. The important parts of the mechanism are **jewel-mounted**. Central pointer **for 1/1000 mm reading**. Outer ring of dial face can be rotated to zero the dial. Nearly constant measuring force over the entire measuring range.

Optional extras:

Special contact points No. 434900; 434910; 434915.

Technical description

Standard	Manufacturer's standard
Measuring range	0 - 1 mm
Graduation	0.001 mm
Clamping shank \varnothing h6	8 mm
Scale divisions	1/1000 mm
Calibration	C2

Reading per pointer revolution	0.2 mm
Gauging force	1.12 - 1.68 N
Body Ø	61.5 mm
Rotatable dial face	yes
Measurement technology	analogue
Material of the housing	Brass
Type of product	dial gauge

Services

CalibrationDial indicator, analogue 0.001 maximum measuring span 5 mm	023020 5
---	----------