



Precision dial indicator IP67, shock-resistant, Measuring range / Body Ø: 10/61,5mm



Order data

Order number	432230 10/61,5
GTIN	7630041151787
Item class	45A

Description

Version:

Dial indicators with protection **against splashed water, oil and dirt**. Contact point on plunger spindle sealed by rubber bellows, sealed by protective sleeve at the top. Back wall sealed, glass and outer ring tightly screwed. Clamping shank Ø 8 mm h6.

Function:

IP67: Protected against intermittent immersion in water and protected against penetration by dust (dust-tight), also completely protected against touching.

Optional extras:

Special contact points No. 434900; 434910; 434915.

Technical description

Standard	DIN 878
Reading per pointer revolution	1 mm
Graduation	0.01 mm
Clamping shank Ø h6	8 mm

IP Index of Protection	IP 67
Body Ø	61.5 mm
Calibration	C1
Gauging force	1.04 - 1.56 N
Scale divisions	1/100 mm
Measuring range	0 - 10 mm
Measurement variation MPE (measurement range)	15 µm
Measurement technology	analogue
Packaging	sturdy box
Type of product	dial gauge

Services

DAkkS calibrationDial indicator analogue 0.01 and digital 0.01 / 0.001 maximum measuring span 12,5 mm	023010 12,5
CalibrationDial indicator analogue 0.01 and digital 0.01 / 0.001 maximum measuring span 10 mm	023000 10