



## small dial indicator IP67, shock-resistant, Measuring range / Body Ø: 5/40



### Order data

Order number	432670 5/40
GTIN	7630041151794
Item class	45A

### Description

#### Version:

Dimensions to DIN EN ISO 463, issue June 2006. Precision small dial indicators with strong metal casing, clamping shank Ø 8 mm h6, hardened and ground. Outer ring of dial face can be rotated to zero the dial. Yellow dial for easier reading.

#### Function:

IP67: Protected against intermittent immersion in water and protected against penetration by dust (dust-tight), also completely protected against touching.

#### Optional extras:

Special contact points No. 434900; 434910; 434915.

### Technical description

Gauging force	0.63 - 0.77 N
Reading per pointer revolution	0.5 mm
IP Index of Protection	IP 67
Clamping shank Ø h6	8 mm
Measuring range	0 - 5 mm

Graduation	0.01 mm
Calibration	C1
Body Ø	40 mm
Rotatable dial face	yes
Measurement technology	analogue
Packaging	sturdy box
Type of product	dial gauge

### Services

CalibrationDial indicator analogue 0.01 and digital 0.01 / 0.001 maximum measuring span 10 mm	023000 10
---	-----------