



## Precision dial indicator, shock-resistant, Measuring range / Body Ø: 1/44,5mm



### Order data

Order number	433407 1/44,5
GTIN	7630041151831
Item class	45A

### Description

#### Version:

Strong, satin chrome plated brass casing; unbreakable dial glass. Clamping shank  $\varnothing$  8 mm h6, hardened and ground. High accuracy version. The important parts of the mechanism are **jewel-mounted**. Central pointer **for 1/1000 mm reading**. Outer ring of dial face can be rotated to zero the dial. Nearly constant measuring force over the entire measuring range.

#### Optional extras:

Special contact points No. 434900; 434910; 434915.

### Technical description

Graduation	0.001 mm
Measuring range	0 - 1 mm
Standard	Manufacturer's standard
Body $\varnothing$	44.5 mm
Reading per pointer revolution	0.2 mm
Calibration	C2

Clamping shank $\varnothing$ h6	8 mm
Gauging force	0.8 - 1.2 N
Scale divisions	1/1000 mm
Rotatable dial face	yes
Measurement technology	analogue
Material of the housing	Brass
Type of product	dial gauge

### Services

CalibrationDial indicator, analogue 0.001 maximum measuring span 5 mm	023020 5
---	----------