



small dial indicator shock-resistant, Measuring range / Body Ø: 5/40



Order data

Order number	432570 5/40
GTIN	7630041109894
Item class	45A

Description

Version:

Dimensions to DIN EN ISO 463, issue June 2006. Precision small dial indicators with strong metal casing, clamping shank \varnothing 8 mm h6, hardened and ground. Outer ring of dial face can be rotated to zero the dial. Yellow dial for easier reading.

Optional extras:

Special contact points No. 434900; 434910; 434915.

Packaging: sturdy box

Calibration: C1

Graduation: 0.01 mm

Reading per pointer revolution: 0.5 mm

Gauging force: 0.63 - 0.77 N

Technical description

Reading per pointer revolution	0.5 mm
Calibration	C1
Graduation	0.01 mm
Measuring range	0 - 5 mm

Body Ø	40 mm
Clamping shank Ø h6	8 mm
Gauging force	0.63 - 0.77 N
Rotatable dial face	yes
shock-resistant	yes
Measurement technology	analogue
Packaging	sturdy box
Type of product	dial gauge

Services

Calibration Dial indicator analogue 0.01 and digital 0.01 / 0.001 maximum measuring span 10 mm	023000 10
DAkkS calibration Dial indicator analogue 0.01 and digital 0.01 / 0.001 maximum measuring span 10 mm	023010 10
Labelling laser-etched Type	018940