

Garant**Reversible precision ratchet, 1/4 inch, Type: 1/4****Order data**

Order number	632345 1/4
GTIN	4062406798413
Item class	61A

Description**Version:**

Material selection and special forging process guarantee optimal functioning and long life. With ejector and reversing lever for right-hand and left-hand threads, working arc 5°.

Standard:

Außenvierkante nach **DIN 3120-A 6,3** mit federnder Kugel, Innenvierkante nach **DIN 3120**.

Material:

Chrome vanadium steel, chrome-plated.

Suitable for:

Manual use.

Technical description

Square drive	1/4 in
overall length	116 mm
No. of teeth	72
Working angle	5 degrees
Material	Chromium vanadium steel
Surface	chrome-plated
with swivel jointed head	no
with swivel head	no
with ejector	yes

with hammer function	no
with QuickRelease	no
Ratchet head can be detached from the handle	no
stepless pull-out	no
Type of product	Ratchet

Accessories

Spare part range, precision ratchet 1/4 inch Type 1/4	632031 1/4
---	------------