

**Garant****Reversible precision ratchet, 3/8 inch, Type: 3/8****Order data**

Order number	635145 3/8
GTIN	4062406798420
Item class	61A

**Description****Version:**

Material selection and special forging process guarantee optimal functioning and long life. With ejector and reversing lever for right-hand and left-hand threads, working arc 5°.

**Standard:**

Außenvierkant nach **DIN 3120-A 10** mit federnder Kugel, für Innenvierkant nach **DIN 3120-C 10** mit Rillen.

**Material:**

Chrome vanadium steel, chrome-plated.

**Suitable for:**

Manual use.

**Technical description**

Square drive	3/8 in
overall length	197 mm
No. of teeth	72
Working angle	5 degrees
Material	Chromium vanadium steel
Type of product	Ratchet

**Accessories**

Spare parts assortment for precision ratchet 3/8 inch Type  
3/8

---

635031 3/8