



Electrician's multi-tool NexStrip®, Type: 1



Order data

| | |
|--------------|---------------|
| Order number | 729501 1 |
| GTIN | 4003773088165 |
| Item class | 73F |

Description

Version:

Very sturdy light-weight body made of glass fibre-reinforced plastic with ergonomic two-component handle. Stripping flexible and solid conductors of 0.03 – 10 mm² (AWG 32 – 8). Optimum adaptation to special materials or temperature conditions through fine adjustment. Quick and precise square crimping of individual terminal sleeves to DIN 46228 part 1 + 4, from 0.25 – 4 mm². Self-adjusting – permits quick switching between various sizes. With length stop and wire cutter.

Advantage:

Cutting and **stripping** the cable as well as **crimping** of terminal sleeves **with only one tool**, no need for laborious tool changes.

Application:

For wiring electronic devices, such as PLC (programmable logic controller), in household installations or in mobile homes.

Spare part:

Spare blade available under No. 728714 size 10 and length stop available under No. 728715 size 10.

Technical description

| | |
|---|---------------------------|
| for conductor cross-section (crimping) | 0.25 - 4 mm ² |
| for conductor cross-section (cutting and stripping) | 0.03 - 10 mm ² |

| | |
|-----------------|---------------|
| overall length | 190 mm |
| Type of product | Crimping tool |

Accessories

| | |
|--|-----------|
| Blade for wire stripping tool for conductor cross-section 10 mm ² | 728714 10 |
| Length stop for wire stripping tool for conductor cross-section 10 mm ² | 728715 10 |