

**Diamond cutting disc STANDARD** Universal, Disc Ø: 115mm****Order data**

Order number	569721 115
GTIN	9003173102909
Item class	53T

Description**Version:**

Diamond cutting discs for wet and dry cutting. Bore Ø 22.23 mm.

- **High cutting performance of diamonds gives short cutting times.**
- **Extremely long working life, fewer disc changes.**
- **Unvarying diameter, always cuts to the full depth.**
- **Hardly any disc wear, reducing dust generation.**

For everyday use on all building materials such as concrete, bricks, natural stone etc. Directly sintered coating, hardened body (no wandering).

Application:

For cutting all common building materials such as concrete (even reinforced), bricks, natural stone, tiles, ceramics, steel etc.

Note:

- **Diamond coating already pre-sharpened. Observe correct direction of rotation!**
- **Other diamond cutting discs on request.**

Technical description

Disc Ø	115 mm
--------	--------

maximum speed	13300 min ⁻¹
Abrasive coating width	2 mm
Abrasive coating height	7 mm
Bore Ø	22.23 mm
Grinding media	Diamond
Grinding medium code	D
optimised for material	Stone
Shape	41
Shape description	straight
Propulsive equipment	Angle grinder
maximum circumferential speed	80 m/s
Type of product	Cutting disc