

Drum unwinder, Type: 500/M



Order data

| | |
|--------------|---------------|
| Order number | 992900 500/M |
| GTIN | 2050002064430 |
| Item class | 960 |

Description

Version:

Compact drum unwinder with loading ramp for cable drums made of wood, steel or plastic. Easy, twist-free unwinding of the cable drum. High-quality, adjustable carrying rollers with ball bearings. Suitable for indoor use only. With 4 braked castors.

Colour:

Mouse grey RAL 7005

Note:

The drum weights apply only to non-continuous unwinding with undamaged drums.

Technical description

| | |
|----------------------------|---------------|
| Height | 80 mm |
| Weight | 10 kg |
| Maximum drum weight | 140 kg |
| Width | 550 mm |
| Maximum drum width | 520 mm |
| Depth | 530 mm |
| Drum Ø | 150 - 700 mm |
| Manufacturer's designation | TROMBOI 500 M |

Type of product

Drum unwinder