



DUO-LOCK extension, cylindrical, steel, short Plain shank, DUO-LOCK interface: DL16



Order data

Order number	220372 DL16
GTIN	4034221149947
Item class	26Y

Description

Version:

Coated for optimum shrinking in and out.

Technical description

Ø D ₂	15.5 mm
L ₂	8 mm
Overall length L	65 mm
Recommended torque	60 Nm
Shank Ø D _s	16 mm
DUO-LOCK interface	DL16
Through-coolant	yes
Type of product	Threaded copy mill arbor