



DUO-LOCK extension, cylindrical, steel, short SAFE-LOCK, DUO-LOCK interface: DL12



Order data

Order number	220370 DL12
GTIN	4034221149909
Item class	26Y

Description

Version:

Coated for optimum shrinking in and out.

Technical description

Ø D ₂	11.5 mm
Overall length L	65 mm
L ₂	6 mm
Shank Ø D _s	12 mm
Recommended torque	30 Nm
DUO-LOCK interface	DL12
Through-coolant	yes
Type of product	Threaded copy mill arbor