



DUO-LOCK extension, cylindrical, steel, long Plain shank, DUO-LOCK interface: DL20



Order data

Order number	220374 DL20
GTIN	4034221129635
Item class	26Y

Description

Version:

Coated for optimum shrinking in and out.

Technical description

Ø D ₂	19.3 mm
Overall length L	200 mm
L ₂	10 mm
Recommended torque	80 Nm
Shank Ø D _s	20 mm
DUO-LOCK interface	DL20
Through-coolant	yes
Type of product	Threaded copy mill arbor