



DUO-LOCK extension, cylindrical, steel, long Plain shank, DUO-LOCK interface: DL10



Order data

Order number	220374 DL10
GTIN	4034221149879
Item class	26Y

Description

Version:

Coated for optimum shrinking in and out.

Technical description

Overall length L	100 mm
Ø D ₂	9.6 mm
L ₂	5 mm
Shank Ø D _s	10 mm
Recommended torque	20 Nm
DUO-LOCK interface	DL10
Through-coolant	yes
Type of product	Threaded copy mill arbor