



## DUO-LOCK extension, cylindrical, steel, long Plain shank, DUO-LOCK interface: DL12



### Order data

Order number	220374 DL12
GTIN	4034221149923
Item class	26Y

### Description

**Version:**

Coated for optimum shrinking in and out.

### Technical description

Overall length L	120 mm
Ø D <sub>2</sub>	11.5 mm
L <sub>2</sub>	6 mm
Shank Ø D <sub>s</sub>	12 mm
Recommended torque	30 Nm
DUO-LOCK interface	DL12
Through-coolant	yes
Type of product	Threaded copy mill arbor